




EE851



## Motion detector comfort 140° anthracite

### Technical properties

#### Architecture

Bus system Without

#### Functions

Function Presence simulation ; can be used as a single unit, main device or extension unit

#### Dimensions

Height of installed product 2.5 mm

Recommended installation height 2.5 m

#### Reach distance

Range, side each ≈ 6 m

#### Power supply

Supply voltage 230 V +10% / -15%

#### Detection

Detection angle 140 °

Detection angle 140 °

Frontal detecting distance 16 m

Side detecting distance 10 m

#### Materials

Material plastic

#### Lighting control

Response brightness, adjustable ≈ 5...1000 lx

Brightness measurement range 5 / 1000 Lux

#### LED control

230V LED lamps 20 x 20 W

LED with LED detection and mode indicator

#### Installation, mounting

Maximum Mounting Height 4 m

Installation mode for wall and ceiling mounting, corner installation with adapter

#### Connection

Type of connection with screw terminals

#### Settings

Response value sensitivity adjustable	Yes
Delay time, adjustable	5 s...30 mn
Setting	with potentiometers for setting the response brightness and delay time without dismantling
<b>Scope of delivery</b>	
Component	with fitting material
<b>Equipment</b>	
Remote controllable	EE806
Angle of horizontal detection	140 °
Slewing	vertically slewing and horizontally rotating
<b>Use conditions</b>	
Operating temperature	-20...55 °C
Storage/transport temperature	-20...60 °C
Energy-saving	low intrinsic energy requirement ; energy saving by means of presence and brightness-dependent ON and OFF switching of light
<b>Identification</b>	
Application, usage	Motion detector
Main design line	Motion detectors