



EPN541



## Latching relay 4NO 24V

### Technical properties

#### Functions

Max. temporisation	60 s
--------------------	------

#### Configuration

Number of modules	2
-------------------	---

#### Main electrical features

Rated operational voltage Ue	250 / 400 V
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	400 V
DC control voltage	12 V
Command voltage AC	24 V

#### Electric current

Quiescent current	6 mA
Rated current	16 A

#### Dimensions

Depth of installed product	63 mm
Height of installed product	83 mm
Width of installed product	35 mm

#### Frequency

Frequency	50 to 60 Hz
-----------	-------------

#### Power

Inrush power absorbed	55 VA
Total power loss under IN	4.8 W

#### Resistance

Winding resistance	6.4 Ω
--------------------	-------

#### Endurance

Electrical durability at nominal load in AC21in operating cycles	150000
Number of mechanical operations	500000

#### Fluorescent bulbs control

Max. power with fluorescent parallel lamps	900 VA
--	--------

**Incandescent bulbs control**

Max. power with incandescent lamps	1800 W
------------------------------------	--------

**Installation, mounting**

Tightening torque	1,6Nm
-------------------	-------

**Connection**

Connection cross-sect. flexible conductor	1 / 6mm <sup>2</sup>
---	----------------------

Connection cross-sect. rigid cable	1,5 / 10mm <sup>2</sup>
------------------------------------	-------------------------

Number of contacts	4
--------------------	---

Type of contacts	4NO
------------------	-----

Type of connection	with screw
--------------------	------------

**Equipment**

Type of latching relay	electromechanic
------------------------	-----------------

**Use**

Pulse duration	50 ms
----------------	-------

**Standards**

Standard text	IEC/EN 60669-2
---------------	----------------

**Use conditions**

Operating temperature	-5...40 °C
-----------------------	------------

Storage/transport temperature	-40...80 °C
-------------------------------	-------------

Manual operation possible	Yes
---------------------------	-----