




EE804



IP21

Detector 360° wall mounted

Technical properties

Architecture

Fixing mode	surface-mounting
-------------	------------------

Functions

Function	can only be used as individual unit
----------	-------------------------------------

Main electrical features

Rated operational voltage U _e	230 V
Frequency	50 Hz

Dimensions

Height of installed product	50 mm
Dimensions (Ø x H)	100 x 50 mm
Width of installed product	105.5 mm
Recommended installation height	2.5...3.5 m

Power supply

Supply voltage	230 V +10% / -15%
----------------	-------------------

Detection

Detection angle	360 °
Detection angle	360 °
Detection field Ø, on floor	≈ 6 m
Frontal detecting distance	6 m
Side detecting distance	6 m

Materials

Colour	white
RAL colour	RAL 9001 - Cream
Material	plastic

Lighting control

Response brightness, adjustable	≈ 5...1000 lx
Brightness measurement range	5 / 1000 Lux

Installation, mounting

Maximum Mounting Height	4 m
Mounting type	surface-mounted

Connection

Number of contacts	1
--------------------	---

Type of connection

with screw terminals

Settings

Response value sensitivity adjustable	No
Delay time, adjustable	5 s...15 mn

Scope of delivery

Component	with fitting material
-----------	-----------------------

Equipment

Angle of horizontal detection	360 °
-------------------------------	-------

Safety

Protection class	isol.class II
------------------	---------------

Use conditions

Operating temperature	0...45 °C
Storage/transport temperature	-20...60 °C

Identification

Application, usage	Motion detector
Main design line	Motion detectors