




EPN510



## Latching relay 1NO 230V

### Technical properties

#### Functions

Max. temporisation	60 s
--------------------	------

#### Configuration

Number of modules	1
-------------------	---

#### Main electrical features

Rated operational voltage Ue	250 V
------------------------------	-------

#### Voltage

Rated insulation voltage	250 V
DC control voltage	110 V
Command voltage AC	230 V

#### Electric current

Quiescent current	6 mA
Rated current	16 A

#### Dimensions

Depth of installed product	63 mm
Height of installed product	83 mm
Width of installed product	17.5 mm

#### Frequency

Frequency	50 to 60 Hz
-----------	-------------

#### Power

Inrush power absorbed	25 VA
Total power loss under IN	1.2 W

#### Resistance

Winding resistance	1225 Ω
--------------------	--------

#### Endurance

Electrical durability at nominal load in AC21in operating cycles	150000
Number of mechanical operations	500000

#### Fluorescent bulbs control

Max. power with fluorescent parallel lamps	900 VA
--	--------

#### Incandescent bulbs control

Max. power with incandescent lamps

1800 W

---

**Installation, mounting**

Tightening torque

1,6Nm

---

**Connection**

Connection cross-sect. flexible conductor

1 / 6mm<sup>2</sup>

Connection cross-sect. rigid cable

1,5 / 10mm<sup>2</sup>

Number of contacts

1

Type of contacts

1NO

---

**Equipment**

Type of latching relay

electromechanic

---

**Use**

Pulse duration

50 ms

---

**Standards**

Standard text

IEC/EN 60669-2

European directive WEEE

concerned

---

**Use conditions**

Operating temperature

-5...40 °C

Storage/transport temperature

-40...80 °C

Manual operation possible

Yes