



EVN011



**IP20**

## Remote Control Dimmer universal 300W

### Technical properties

#### Architecture

Type of order Push button

#### Configuration

Number of modules 1

#### Main electrical features

Rated operational voltage  $U_e$  230 V

Frequency 50/60 Hz

#### Voltage

Operating voltage 230 V~ +10%/-15%

#### Fuse

Fuse with electronic short-circuit and overload protection

#### Dimensions

Depth of installed product 65 mm

Height of installed product 90 mm

Installation height 0 / 1000 m

Width of installed product 17.5 mm

Width of rail mounted device (RMD) 1 modules

#### Length

Max distance to switches 50 mm

#### Power

Dimmable conventional transformers 300 VA

Halogen switching capacity 230V 300 W

Power consumed 2.1 W

Power consumption (operation) 2.1 W

Incandescent bulb power 300 W

Total power loss under IN 0.2 W

Conventional transformers 300 VA

Electronic transformers 300 W

#### Cover, door

Surface cover Other

#### Materials

Surface appearance matt

**Fluorescent bulbs control**

Dimmable energy-saving lamps	60 W
Lighting power fluocompact lamps with built-in ballast	60 W

**LED control**

Quantity of dimmable, 230 V retrofit LED lamps	max. 8
Max number of LED/CFL lamps	8
Dimmable 230 V LED lamps	60 W
Power LED	60 W

**Incandescent bulbs control**

Max. power with incandescent lamps	300 W
230 V incandescent lamps and halogen lamps	300 W

**Installation, mounting**

Fixing type	With claws
Mounting type	din-Rail
Installation mode	for mounting on DIN rail

**Connection**

Connection cross-sect. flexible conductor	1,5 / 6mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 6mm <sup>2</sup>
Type of load	universal
Conductor cross-section (flexible)	1.5...6 mm <sup>2</sup>
Conductor cross-section (rigid)	1.5...6 mm <sup>2</sup>
Type of connection	with screw terminals
Type of connection	with screw

**Cable**

Load cable length	max. 50 m
-------------------	-----------

**Equipment**

Type of dimmer	No
Dimming principle	automatic load detection

**Safety**

REACH conform	No
Halogen free	No

**Use conditions**

Operating temperature	-10...45 °C
Storage/transport temperature	-25...70 °C

**Instructions**

Information text	Only for use with dimmable lamps!
------------------	-----------------------------------