



HHA033Z

**Moulded Case Circuit Breaker x160 4P 25kA 32A**

**Technical properties**

**Architecture**

Type of order	Toggle
Number of poles	4 P
Type of pole	4P4D

**Functions**

Complete device with protection unit	Yes
Trip Unit	TM F/F
With integrated earth leakage fault protection	No

**Configuration**

Number of modules	6
-------------------	---

**Main electrical features**

Rated operational voltage Ue	220 / 415 V
Frequency	50/60 Hz

**Voltage**

Rated insulation voltage	690 V
Rated impulse withstand voltage	8 kV
With under voltage release	No

**Electric current**

Rated current	32 A
Rated ultimate short-circuit breaking capacity Icu under 690V AC IEC 60947-2	4 kA
Thermal protection nob setting xIN	1
Thermal setting current on neutral pole	1 In
Breaking capacity on 1 pole for IT 230V NF 60947-2	21 kA
Breaking capacity on 1 pole for IT 400V NF 60947-2	9 kA
Rated service breaking capacity Ics AC according IEC 60947-2	80 %
Rated ultimate short-circuit breaking capacity Icu under 230V AC IEC 60947-2	35 kA
Rated ultimate short-circuit breaking capacity Icu under 240V AC IEC 60947-2	35 kA
Rated ultimate short-circuit breaking capacity Icu under 400V AC IEC 60947-2	25 kA
Rated ultimate short-circuit breaking capacity Icu under 415V AC IEC 60947-2	25 kA

### Current correction factors

Correction factor of rating current for 2 devices placed side-by-side	1
Correction factor of rating current for 3 devices placed side-by-side	1
Correction factor of rating current for 4 and 5 devices placed side-by-side	1
Correction factor of rating current for 6 devices placed side-by-side	1

### Power

Total power loss under IN	8.4 W
Power loss per pole at In	2.8 W

### Tripping

Tripmode	TM
Thermal protection trip time	0 ms
Time of response when opening	10 ms

### Electrical specifications

Magnetic trip delay time	0 ms
--------------------------	------

### Endurance

Electric endurance in number of cycles	1000
Number of mechanical operations	4000

### Installation, mounting

DIN rail mounting with optional adaptor	Yes
---	-----

### Connection

Connection cross-sect. flexible conductor	4 / 70mm <sup>2</sup>
Connection cross-sect. rigid cable	4 / 95mm <sup>2</sup>
Connection	Front connection
Type of connection	with screw

### Settings

Range of the magnetic adjustment	600 A
Setting type In or Ith	IN

### Equipment

Number of auxiliary contacts as normally closed contact	0
Number of auxiliary contacts as normally open contact	0
Number of auxiliary contacts as change-over contact	0
Motor drive optional	No

### Use cases

Category of use	A
-----------------	---

---

**Standards**

Standard text	IEC 60947-2
---------------	-------------

---

European directive WEEE	not concerned
-------------------------	---------------

**Use conditions**

---

Altitude	2000 m
----------	--------

---

Air humidity protection	for all climates
-------------------------	------------------