



LS501



## Fuse carrier 1P 32A 690V L38 1M

### Technical properties

#### Architecture

Number of poles	1 P
Type of pole	1 P

#### Configuration

Number of modules	1
-------------------	---

#### Main electrical features

Type of supply voltage	AC
------------------------	----

#### Voltage

Rated insulation voltage	690 V
--------------------------	-------

#### Electric current

Rated current	32 A
---------------	------

#### Fuse

CharactFuse	gG ; aM
Fuse Size	10.3 x 38

#### Dimensions

Depth of installed product	75 mm
Height of installed product	83 mm
Width of installed product	18 mm

#### Frequency

Frequency	50 to 60 Hz
-----------	-------------

#### Power

Total power loss under IN	7.4 W
---------------------------	-------

#### Installation, mounting

Tightening torque	2,2Nm
-------------------	-------

#### Equipment

Can be accessorized	Yes
---------------------	-----

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

Protection index IP	IP20
---------------------	------

REACH conform	Yes
RoHS conform	Yes
<b>Use conditions</b>	
Operating temperature	-5...50 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Storage/transport temperature	-25...80 °C