



LS501



Fuse carrier 1P 32A 690V L38 1M

Technical properties

Architecture

Number of poles	1 P
Type of pole	1 P

Configuration

Number of modules	1
-------------------	---

Main electrical features

Type of supply voltage	AC
------------------------	----

Voltage

Rated insulation voltage	690 V
--------------------------	-------

Electric current

Rated current	32 A
---------------	------

Fuse

CharactFuse	gG ; aM
Fuse Size	10.3 x 38

Dimensions

Depth of installed product	75 mm
Height of installed product	83 mm
Width of installed product	18 mm

Frequency

Frequency	50 to 60 Hz
-----------	-------------

Power

Total power loss under IN	7.4 W
---------------------------	-------

Installation, mounting

Tightening torque	2,2Nm
-------------------	-------

Equipment

Can be accessorized	Yes
---------------------	-----

Safety

REACH conform	Yes
RoHS conform	Yes

Use conditions

Operating temperature	-5...50 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Storage/transport temperature	-25...80 °C