



LS503



## Fuse carrier 3P 32A 690V L38 3M

### Technical properties

#### Architecture

Number of poles	3 P
Type of pole	3 P

#### Configuration

Number of modules	3
-------------------	---

#### Main electrical features

Type of supply voltage	AC
------------------------	----

#### Voltage

Rated insulation voltage	690 V
--------------------------	-------

#### Electric current

Rated current	32 A
---------------	------

#### Dimensions

Depth of installed product	75 mm
Height of installed product	83 mm
Width of installed product	54 mm

#### Frequency

Frequency	50 to 60 Hz
-----------	-------------

#### Power

Total power loss under IN	11.1 W
---------------------------	--------

#### Equipment

Can be accessorized	Yes
---------------------	-----

#### Standards

European directive WEEE	concerned
-------------------------	-----------

#### Safety

Protection index IP	IP20
REACH conform	Yes
RoHS conform	Yes

#### Use conditions

Operating temperature	-5...50 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3

