



LVSG2CE

**NH Fuse-switch vertical design LV size 2 185mm 1pole M12**

**Technical properties**

**Architecture**

Number of poles	1 P
Type of pole	1 P

**Configuration**

Distance between rail centre, 40 mm	No
Distance between rail centre, 50 mm	No
Distance between rail centre, 60 mm	No
Distance between rail centre, 100 mm	No
Distance between rail centre, 185 mm	Yes

**Main electrical features**

Rated operational voltage Ue	690 V
Frequency	50/60 Hz

**Voltage**

Rated insulation voltage	1000 V
Rated impulse withstand voltage	12 kV

**Electric current**

Cut off current	120 kA
Rated current for Ue=400V AC according to IEC 61439-1 5.3.2	400 A
Rated current for Ue=500V AC according to IEC 61439-1 5.3.2	400 A
Rated current for Ue=690V AC according to IEC 61439-1 5.3.2	400 A
Rated current	400 A
Rated short-time withstand current 1s	10 kA
Rated conditional short-circuit current for Ue=400V IEC 61439-1 3.8.10.4	120 kA
Rated conditional short-circuit current for Ue=690V IEC 61439-1 3.8.10.4	100 kA
Fuse-links test rated cond. short-circuit current Ue=400V IEC 61439-1 3.8.10.4	400 A
Fuse-links test rated cond. short-circuit current Ue=500V IEC 61439-1 3.8.10.4	400 A
Fuse-links test rated cond. short-circuit current Ue=690V IEC 61439-1 3.8.10.4	315 A
Conventional free air thermal current with Trennmesser and std. cross section	480 A
Conv. free air therm.current w/fuse-links and std.cross sect. IEC60947-1 4.3.2.1	400 A

Acceptable current rating with AC22 category B	400 A
Acceptable current rating with AC23 category B	400 A
Rated conditional short-circuit current for Ue=500V IEC 61439-1 3.8.10.4	120 kA
<b>Electric current / temperature</b>	
Rating current 40°C	400 A
Rating current 45°C	380 A
Rating current 50°C	360 A
Rating current 55°C	340 A
Rating current 60°C	320 A
Rating current 65°C	300 A
Rating current 70°C	280 A
<b>Fuse</b>	
Fuse Size	NH2
<b>Dimensions</b>	
Depth of installed product	190 mm
Height of installed product	671 mm
Length	671 mm
Width of installed product	100 mm
Width of the busbars	5 / 10 mm
Busbar distance	185 mm
<b>Power</b>	
Total power loss under IN	56 W
Loss power at full load	158 W
Maximum Power loss of the Fuse-Link installed in device	34 W
Dissipated energy in cable	86 W
<b>Endurance</b>	
Electric endurance in number of cycles	200
Number of mechanical operations	800
Total service life (mechanical and electrical endurance) IEC 60947-3 Table 4	1000
<b>Materials</b>	
Copper weight of the product	2122 g
Silver weight of the product	2.18 g
Material	Plastic/metal
<b>Installation, mounting</b>	
Tightening torque	32Nm
Torque at mounting on busbar	32 Nm
<b>Connection</b>	
Connection cross-sect. flexible conductor	70 / 300mm <sup>2</sup>
Connection cross-sect. rigid cable	150 / 300mm <sup>2</sup>

Subject to technical modifications

Type of connection

screw

### Standards

Rated duties according to IEC 60947-1 4.3.4	Continuous operation
Operation of switching devices according to IEC 60947-1 2.4	depending manual operation (of a mechanical switching device)
Utilisation category for Ue=400V AC according to IEC 60947-3 Table 5	AC-23B
Utilisation category for Ue=500V AC according to IEC 60947-3 Table 5	AC-22B
Utilisation category for Ue=690V AC according to IEC 60947-3 Table 5	AC-21B
European directive WEEE	concerned
Standard cross section according to IEC 60947-1 Tables 9 and 10	240 mm <sup>2</sup>

### Safety

Protection index IP	IP2X
---------------------	------

### Use conditions

Operating temperature	-25...55 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	3
Storage/transport temperature	-40...70 °C