




MZ201



Auxiliary contact 1C+1O 6A 240V AC

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Configuration

Number of modules	0.5
-------------------	-----

Main electrical features

Rated operational voltage U_e	230 / 415 V
---------------------------------	-------------

Type of supply voltage	AC
------------------------	----

Voltage

Rated insulation voltage	4000 V
--------------------------	--------

Max operating voltage	240 V
-----------------------	-------

Rated operational voltage in DC	12 / 250 V
---------------------------------	------------

Electric current

Acceptable current rating with AC1	6 A
------------------------------------	-----

Rated current	6 A
---------------	-----

$I_{min}=f(U=12V\ DC)$ for power circuit	0.3 A
--	-------

$I_{min} = f(U = 230\ V\ DC)$	0.6 A
-------------------------------	-------

$I_{min}=f(U=400V\ AC)$ for power circuit	3 A
---	-----

Dimensions

Depth of installed product	40 mm
----------------------------	-------

Height of installed product	80 mm
-----------------------------	-------

Width of installed product	9.5 mm
----------------------------	--------

Power

Total power loss under IN	0.1 W
---------------------------	-------

Endurance

Electric endurance in number of cycles	6000
--	------

Number of mechanical operations	12000
---------------------------------	-------

Installation, mounting

Tightening torque	1,2Nm
-------------------	-------

Factory fitted	No
----------------	----

Connection

Connection cross-sect. flexible conductor	6mm ²
---	------------------

Connection cross-sect. rigid cable	10mm ²
------------------------------------	-------------------

Type of contacts	1NC+1NO
Type of connection	with screw
Equipment	
Quantity of NC contacts	1
Quantity of NO contacts	1
Quantity of INV contacts	0
Safety	
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Use conditions	
Operating temperature	-25...60 °C
Air humidity protection	95% / 80°C
Storage/transport temperature	-40...80 °C