




MZ201



Auxiliary contact 1C+1O 6A 240V AC

Technical properties

Architecture

Fixing mode	Clipped
-------------	---------

Configuration

Number of modules	0.5
-------------------	-----

Main electrical features

Rated operational voltage Ue	230 / 415 V
Type of supply voltage	AC

Voltage

Rated insulation voltage	4000 V
Max operating voltage	240 V
Rated operational voltage in DC	12 / 250 V

Electric current

Acceptable current rating with AC1	6 A
Rated current	6 A
I _{min} =f(U=12V DC) for power circuit	0.3 A
I _{min} = f (U = 230 V DC)	0.6 A
I _{min} =f(U=400V AC) for power circuit	3 A

Dimensions

Depth of installed product	40 mm
Height of installed product	80 mm
Width of installed product	9.5 mm

Power

Total power loss under IN	0.1 W
---------------------------	-------

Endurance

Electric endurance in number of cycles	6000
Number of mechanical operations	12000

Installation, mounting

Tightening torque	1,2Nm
Factory fitted	No

Connection

Connection cross-sect. flexible conductor	6mm ²
Connection cross-sect. rigid cable	10mm ²

Type of contacts	1NC+1NO
Type of connection	with screw
Equipment	
Quantity of NC contacts	1
Quantity of NO contacts	1
Quantity of INV contacts	0
Safety	
REACH conform	Yes
RoHS conform	Yes
Halogen free	No
Use conditions	
Operating temperature	-25...60 °C
Air humidity protection	95% / 80°C
Storage/transport temperature	-40...80 °C
Identification	
Aesthetic for B.G. Protection devices	FD