



NBN132



## MCB 1P 10kA B-32A 1M

### Technical properties

#### Architecture

Neutral position	without neutral
Number of protected poles	1
Number of poles	1 P
Type of pole	1 P
Curve	B

#### Functions

Concurrently switching N-neutral	No
----------------------------------	----

#### Configuration

Number of modules	1
-------------------	---

#### Connectivity

Top connection alignment for modular devices	Aligned terminal
Bottom connection alignment for modular devices	Aligned terminal

#### Main electrical features

Rated short circuit breaking capacity $I_{cn}$ AC according IEC60898-1	10 kA
Rated operational voltage $U_e$	230 / 400 V
Type of supply voltage	AC
Frequency	50/60 Hz

#### Voltage

Rated insulation voltage	500 V
Rated impulse withstand voltage	6000 V
Minimum threshold voltage ( $U_e$ min)	12 V

#### Electric current

Rated current	32 A
Rated service breaking capacity $I_{cs}$ AC according IEC 60898-1	7.5 kA
min/maxi threshold value of the AC thermal operation	1.13 / 1.45 $I_n$
Magnetic regulating current	3 / 5 $I_n$
min/maxi threshold value of the DC magnetic operation	4 / 7 $I_n$
min/maxi threshold value of the DC thermal operation	1.13 / 1.45 $I_n$

Breaking capacity on 1 pole for IT 400V NF 60947-2	3 kA
Rated short circuit breaking capacity I <sub>cn</sub> under 230V AC according IEC60898-1	10 kA
Rated short circuit breaking capacity I <sub>cn</sub> under 240V AC according IEC 60898-1	10 kA
<b>Electric current / temperature</b>	
Rating current -25°C	39.5 A
Rating current -20°C	38.88 A
Rating current -15°C	38.25 A
Rating current -10°C	37.6 A
Rating current -5°C	36.95 A
Rating current 0°C	36.28 A
Rating current 5°C	35.61 A
Rating current 10°C	34.91 A
Rating current 15°C	34.21 A
Rating current 20°C	33.49 A
Rating current 25°C	32.75 A
Rating current 30°C	32 A
Rating current 35°C	31.23 A
Rating current 40°C	30.44 A
Rating current 45°C	29.63 A
Rating current 50°C	28.79 A
Rating current 55°C	27.93 A
Rating current 60°C	27.04 A
Rating current 65°C	26.13 A
Rating current 70°C	25.18 A
<b>Current correction factors</b>	
Correction factor of rating current for 2 devices placed side-by-side	1
Correction factor of rating current for 3 devices placed side-by-side	0.95
Correction factor of rating current for 4 and 5 devices placed side-by-side	0.9
Correction factor of rating current for 6 devices placed side-by-side	0.85
Correction factor of magnetic tripping with 100 Hz	1.1
Correction factor of magnetic tripping with 200 Hz	1.2
Correction factor of magnetic tripping with 400 Hz	1.5
Correction factor of magnetic tripping with 60 Hz	1.1
<b>Dimensions</b>	
Depth of installed product	70 mm
Height of installed product	83 mm
Width of installed product	17.5 mm
<b>Frequency</b>	

Subject to technical modifications

Frequency

50 to 60 Hz

### Power

Total power loss under IN	3.65 W
Power loss per pole at In	3.65 W

### Endurance

Electric endurance in number of cycles	4000
Number of mechanical operations	20000

### Installation, mounting

Type of top connection for modular devices	with screw
Tightening torque	2,8Nm
Type of top rail clip for modular devices	NA
Type of bottom rail clip for modular devices	plastic
Type of Bottom Connection for modular devices	BIconnect
Top removability for modular devices	Yes
Bottom removability for modular devices	Yes

### Connection

Connection cross-sect. flexible conductor	1 / 25mm <sup>2</sup>
Connection cross-sect. rigid cable	1 / 35mm <sup>2</sup>
Connection cross-section of input and output with screws, for massive conductors	1 / 35 mm <sup>2</sup>
Connection cross section of access and exit with screws, for flexible conductor	1 / 25 mm <sup>2</sup>
Type of connection	with screw

### Standards

Standard text	EN 60898-1
---------------	------------

### Use conditions

Operating temperature	-25...70 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Class of energy limitation I <sup>2</sup> t	3
Altitude	2000 m
Air humidity protection	for all climates
Storage/transport temperature	-25...80 °C