



SBN316

### 3-pole, 16A Modular Switch

#### Technical properties

##### Architecture

Type of order	Break switch
Neutral position	without neutral
Number of poles	3 P
Type of pole	3 P

##### Configuration

Number of modules	2
-------------------	---

##### Main electrical features

Rated operational voltage Ue	400 V
Frequency	50/60 Hz

##### Voltage

Rated insulation voltage	440 V
Type of voltage input 1	AC
Rated impulse withstand voltage	4000 V

##### Electric current

Rated operational current in AC21category B	16 A
Acceptable current rating with AC22 category A	16 A
Rated current	16 A
Rated short-time withstand current 1s	0.24 kA
Thermal rated current outside of housings	16 A
Rated operational current in AC21 category A	16 A
Acceptable current rating with AC22 category B	16 A

##### Dimensions

Depth of installed product	68 mm
Height of installed product	83 mm
Width of installed product	35 mm

##### Frequency

Frequency	50 to 60 Hz
-----------	-------------

##### Power

Total power loss under IN	1.2 W
Power loss per pole at In	0.4 W

**Endurance**

Electrical durability at nominal load in AC21 in operating cycles	25000
Electrical durability at nominal load in AC22 in operating cycles	25000
Number of mechanical operations	200000

**Installation, mounting**

Tightening torque	1,8Nm
-------------------	-------

**Connection**

Connection cross-sect. flexible conductor	1,5 / 10mm <sup>2</sup>
Connection cross-sect. rigid cable	1,5 / 16mm <sup>2</sup>
Cage clamp position	off set
Type of connection	with screw

**Equipment**

Quantity of NC contacts	0
Quantity of NO contacts	3
Quantity of INV contacts	0

**Standards**

Standard text	IEC 60947-3 ; IEC/EN 60669-2 ; IEC/EN 60669-4
European directive WEEE	concerned

**Safety**

Protection index IP	IP20
---------------------	------

**Use conditions**

Operating temperature	-20...50 °C
Degree of pollution according to IEC 60664 / IEC 60947-2	2
Altitude	2000 m
Storage/transport temperature	-40...80 °C