


NCN304



MCB 3P 10kA C-4A 3M

Technical properties

Architecture

| | |
|---------------------------|-----------------|
| Neutral position | without neutral |
| Number of protected poles | 3 |
| Number of poles | 3 P |
| Type of pole | 3 P |
| Curve | C |

Functions

| | |
|----------------------------------|----|
| Concurrently switching N-neutral | No |
|----------------------------------|----|

Configuration

| | |
|-------------------|---|
| Number of modules | 3 |
|-------------------|---|

Connectivity

| | |
|---|------------------|
| Top connection alignment for modular devices | Aligned terminal |
| Bottom connection alignment for modular devices | Aligned terminal |

Main electrical features

| | |
|--|-------|
| Rated short circuit breaking capacity I_{cn} AC according IEC60898-1 | 10 kA |
| Rated operational voltage U_e | 415 V |
| Type of supply voltage | AC |

Voltage

| | |
|--|--------|
| Rated insulation voltage | 500 V |
| Max operating voltage | 440 V |
| Rated impulse withstand voltage | 6000 V |
| Minimum threshold voltage (U_e min) | 12 V |

Electric current

| | |
|---|-------------------|
| Rated current | 4 A |
| Rated service breaking capacity I_{cs} AC according IEC 60898-1 | 7.5 kA |
| min/maxi threshold value of the AC thermal operation | 1.13 / 1.45 I_n |
| Magnetic regulating current | 5 / 10 I_n |
| min/maxi threshold value of the DC magnetic operation | 7 / 15 I_n |
| min/maxi threshold value of the DC thermal operation | 1.13 / 1.45 I_n |

| | |
|--|--------|
| Rating current -10°C according to IEC 60947 | 5.13 A |
| Rating current -15°C according to IEC 60947 | 5.21 A |
| Rating current -20°C according to IEC 60947 | 5.29 A |
| Rating current -25°C according to IEC 60947 | 5.37 A |
| Rating current -5°C according to IEC 60947 | 5.04 A |
| Rating current 0°C according to IEC 60947 | 4.96 A |
| Rating current 10°C according to IEC 60947 | 4.78 A |
| Rating current 15°C according to IEC 60947 | 4.69 A |
| Rating current 20°C according to IEC 60947 | 4.6 A |
| Rating current 25°C according to IEC 60947 | 4.5 A |
| Rating current 30°C according to IEC 60947 | 4.41 A |
| Rating current 35°C according to IEC 60947 | 4.31 A |
| Rating current 40°C according to IEC 60947 | 4.21 A |
| Rating current 45°C according to IEC 60947 | 4.11 A |
| Rating current 5°C according to IEC 60947 | 4.87 A |
| Rating current 50°C according to IEC 60947 | 4 A |
| Rating current 55°C according to IEC 60947 | 3.87 A |
| Rating current 60°C according to IEC 60947 | 3.74 A |
| Rating current 65°C according to IEC 60947 | 3.6 A |
| Rating current 70°C according to IEC 60947 | 3.46 A |
| Rated short circuit breaking capacity I_{cn} under 230V AC according IEC60898-1 | 10 kA |
| Rated short circuit breaking capacity I_{cn} under 400V AC according IEC60898-1 | 10 kA |
| Rated ultimate short-circuit breaking capacity I_{cu} under 230V AC IEC 60947-2 | 30 kA |
| Rated ultimate short-circuit breaking capacity I_{cu} under 240V AC IEC 60947-2 | 30 kA |
| Rated ultimate short-circuit breaking capacity I_{cu} under 400V AC IEC 60947-2 | 15 kA |
| Rated ultimate short-circuit breaking capacity I_{cu} under 415V AC IEC 60947-2 | 15 kA |
| Rated short circuit breaking capacity I_{cn} under 240V AC according IEC 60898-1 | 10 kA |
| Rated short circuit breaking capacity I_{cn} under 415V AC according IEC 60898-1 | 10 kA |
| Rated ultimate short-circuit breaking capacity I_{cu} under 220V AC IEC 60947-2 | 30 kA |
| Rated ultimate short-circuit breaking capacity I_{cu} under 380V AC IEC 60947-2 | 15 kA |
| Electric current / temperature | |
| Rating current -25°C | 4.88 A |
| Rating current -20°C | 4.8 A |
| Rating current -15°C | 4.73 A |
| Rating current -10°C | 4.65 A |
| Rating current -5°C | 4.58 A |
| Rating current 0°C | 4.5 A |
| Rating current 5°C | 4.42 A |

Subject to technical modifications

| | |
|---------------------|--------|
| Rating current 10°C | 4.34 A |
| Rating current 25°C | 4.09 A |
| Rating current 30°C | 4 A |
| Rating current 35°C | 3.9 A |
| Rating current 40°C | 3.79 A |
| Rating current 45°C | 3.69 A |
| Rating current 50°C | 3.58 A |
| Rating current 55°C | 3.46 A |
| Rating current 60°C | 3.34 A |
| Rating current 65°C | 3.22 A |
| Rating current 70°C | 3.1 A |

Current correction factors

| | |
|---|------|
| Correction factor of rating current for 2 devices placed side-by-side | 1 |
| Correction factor of rating current for 3 devices placed side-by-side | 0.95 |
| Correction factor of rating current for 4 and 5 devices placed side-by-side | 0.9 |
| Correction factor of rating current for 6 devices placed side-by-side | 0.85 |
| Correction factor of magnetic tripping with 100 Hz | 1.1 |
| Correction factor of magnetic tripping with 200 Hz | 1.2 |
| Correction factor of magnetic tripping with 400 Hz | 1.5 |
| Correction factor of magnetic tripping with 60 Hz | 1.1 |

Dimensions

| | |
|-----------------------------|---------|
| Depth of installed product | 70 mm |
| Height of installed product | 83 mm |
| Width of installed product | 52.5 mm |

Frequency

| | |
|-----------|-------------|
| Frequency | 50 to 60 Hz |
|-----------|-------------|

Power

| | |
|---|--------|
| Maximum power loss per pole according to the product standard | 3 W |
| Total power loss under IN | 8.18 W |
| Power loss per pole at In | 2.75 W |

Endurance

| | |
|--|-------|
| Electric endurance in number of cycles | 4000 |
| Number of mechanical operations | 20000 |

Installation, mounting

| | |
|--|------------|
| Type of top connection for modular devices | with screw |
| Tightening torque | 2,8Nm |
| Type of top rail clip for modular devices | NA |
| Type of bottom rail clip for modular devices | plastic |

Subject to technical modifications

| | |
|--|------------------------|
| Type of Bottom Connection for modular devices | BIconnect |
| Top removability for modular devices | Yes |
| Bottom removability for modular devices | Yes |
| Suitable for flush-mounting | Yes |
| Connection | |
| Connection cross-section at output with screw, for flexible conductor | 1 / 25 mm ² |
| Connection cross-section at output with screw, for massive conductor | 1 / 35 mm ² |
| Connection cross-section for rigid conductor, upstream terminals with screws | 1 / 35 mm ² |
| Connection cross-section of the access with screws, with flexible conductor | 1 / 25 mm ² |
| Downstream cage clamp delivery status | closed |
| Upstream cage clamp delivery status | opened |
| Equipment | |
| Can be accessorized | Yes |
| Standards | |
| Standard text | EN 60898-1 |
| European directive WEEE | concerned |
| Safety | |
| Protection index IP | IP20 |
| Use conditions | |
| Operating temperature | -25...70 °C |
| Degree of pollution according to IEC 60664 / IEC 60947-2 | 2 |
| Class of energy limitation I ² t | 3 |
| Altitude | 2000 m |
| Storage/transport temperature | -25...80 °C |
| temperatur | |
| Temperature of calibration | 30 °C |