



TH101

Modular USB interface

Technical properties

Architecture

Bus system EIB

Configuration

Number of modules 2

Compatibility

Compatibility compatible with USB 1.1/2.0 transmission protocols

System requirements: system requirements: Windows 2000 or later

Connectivity

Connectors / jacks with B-type USB socket for data traffic (voltage supply via PC)

Voltage

Operating voltage over bus 21...32 V DC

Dimensions

Width of rail mounted device (RMD) 2 modules

Power

Total power loss under IN 0.15 W

Dissipated energy in cable 0.15 W

Storage

Data transmission rate 9.6 kBd

Materials

RAL colour RAL 7035 - Light grey

Connection

Connector type USB connector

Cable

USB cable length max. 5 m

Settings

Supported configuration modes system

Programming programmable from ETS3, V1.0

Equipment

Interface type USB

Software

| | |
|-------------|----------------------------------|
| Update | with flash-controller technology |
| application | bus/PC connection |

Use conditions

| | |
|-----------------------|------------|
| Operating temperature | -5...45 °C |
|-----------------------|------------|

Identification

| | |
|------------------|-----|
| Main design line | KNX |
|------------------|-----|
