



SPA800

**Combined SPD T1+T2 3P Uc 350V Iimp 25kA In 25kA Up 1.5kV TCN with remote contact**

**Technical properties**

**Configuration**

Number of modules 6

**Controls and indicators**

Indicator lamp Optic

**Main electrical features**

Test class type1 IEC61643-11 Yes

Nominal discharge current (In) 8/20µs, IEC 61643)L-N(PEN)/ N-PE 25 / 75 kA

**Electric current**

Calibration of the protection upstream 315 A

Max discharge (Imax) L-N(PEN)/ N-PE 50 kA

**Dimensions**

Depth of installed product 67 mm

Height of installed product 95.2 mm

Width of installed product 106.8 mm

**Electrical specifications**

Signal contact Cross-sections 0.14 / 1.5 mm<sup>2</sup>

Signal contact Current carrying capacity AC/DC 1 / 0.2 A

Signal contact Voltage rating AC/DC 250 / 125 V

**Network configuration**

Network type TN-C

**Installation, mounting**

Tightening torque 4,5Nm

**Standards**

Test class IEC61643-11 / VDE0675-6-11 T1 ; T2

European directive WEEE concerned

**Safety**

REACH conform No

RoHS conform Yes

Halogen free No

**Use conditions**

---

|                               |             |
|-------------------------------|-------------|
| Operating temperature         | -40...80 °C |
| Storage/transport temperature | -40...80 °C |

---