



TCC510S

IP41

## Presence detector 360° monobloc KNX, white

### Technical properties

#### Architecture

Bus system	KNX
------------	-----

#### Functions

Function	Linking several detectors in order to expand the detection area
----------	---

#### Controls and indicators

Button / push-button	with programming button
----------------------	-------------------------

#### Connectivity

Number of binary inputs	0
-------------------------	---

#### Voltage

Operating voltage over bus	21...32 V DC
----------------------------	--------------

#### Electric current

Bus current consumption (data transfer)	10 mA
---	-------

#### Dimensions

Dimensions (Ø x H)	78 x 70 mm
--------------------	------------

Installation opening Ø	60...63 mm
------------------------	------------

Recommended installation height	2.5...3.5 m
---------------------------------	-------------

Installation wall thickness	10...28 mm
-----------------------------	------------

#### Measurement

Detection Method	presence
------------------	----------

#### Detection

Detection angle	360 °
-----------------	-------

Detection angle	360 °
-----------------	-------

Angle of vertical detection	55 °
-----------------------------	------

Detection field Ø, on floor	≈ 7 m
-----------------------------	-------

Detection field Ø, at desk height	≈ 5 m
-----------------------------------	-------

Frontal detecting distance	7 m
----------------------------	-----

Side detecting distance	8 m
-------------------------	-----

#### Materials

Colour	white
--------	-------

RAL colour	RAL 9010 - Pure white
------------	-----------------------

Surface appearance	matt
--------------------	------

**Lighting control**

---

Brightness measurement range	5 / 1000 Lux
------------------------------	--------------

**Installation, mounting**

---

Maximum Mounting Height	4 m
-------------------------	-----

---

Installation mode	with spring clips for ceiling installation
-------------------	--

**Connection**

---

Bus coupling unit	with integral bus coupling unit
-------------------	---------------------------------

---

Bus connection	bus connection via connecting terminal
----------------	--

**Settings**

---

Supported configuration modes	system, easy
-------------------------------	--------------

---

Delay time, adjustable	1 mn...1 h
------------------------	------------

---

Setting	with potentiometers for setting the response brightness and delay time without dismantling
---------	--

**Scope of delivery**

---

Bus connection included	Yes
-------------------------	-----

**Equipment**

---

Number of channels	1
--------------------	---

---

Angle of horizontal detection	360 °
-------------------------------	-------

**Safety**

---

REACH conform	No
---------------	----

---

RoHS conform	Yes
--------------	-----

---

Halogen free	No
--------------	----

**Use conditions**

---

Operating temperature	-10...45 °C
-----------------------	-------------

---

Storage/transport temperature	-20...60 °C
-------------------------------	-------------

---

Energy-saving	energy saving by presence and brightness-controlled lighting control
---------------	--

**Identification**

---

Main design line	KNX
------------------	-----