



TH101

Modular USB interface

Technical properties

Architecture

Bus system EIB

Configuration

Number of modules 2

Compatibility

Compatibility compatible with USB 1.1/2.0 transmission protocols

System requirements: system requirements: Windows 2000 or later

Connectivity

Connectors / jacks with B-type USB socket for data traffic (voltage supply via PC)

Voltage

Operating voltage over bus 21...32 V DC

Dimensions

Width of rail mounted device (RMD) 2 modules

Power

Total power loss under IN 0.15 W

Dissipated energy in cable 0.15 W

Storage

Data transmission rate 9.6 kBd

Materials

RAL colour RAL 7035 - Light grey

Connection

Connector type USB connector

Cable

USB cable length max. 5 m

Settings

Supported configuration modes system

Programming programmable from ETS3, V1.0

Equipment

Interface type USB

Software

Update	with flash-controller technology
application	bus/PC connection

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Identification

Main design line	KNX
------------------	-----
