



TJA470

IK04 IP20

Domovea expert

Technical properties

Architecture

Fixing mode DIN rail type O (symmetrical)

Functions

Function converting

Configuration

Number of modules 6

Controls and indicators

With LED indication Yes

Manual selection switches / push-buttons Selection switch for online/offline mode

Connectivity

Protocol TCP/IP

Connectors / jacks with 2 USB sockets type A

IP Integration of IP cameras into the 2-wire system

Voltage

Operating voltage 24 V DC

Operating voltage 21.6 ... 33 V= or 48 V= Power over Ethernet PoE according to IEEE802.3

Operating voltage over bus 21...32 V DC

Electric current

Current consumption (operation) 0.5 A

Making current 650 mA

Dimensions

Width of rail mounted device (RMD) 6 modules

Power supply

Operating voltage via power supply 24 V DC

Equipment

Demounting protection No

Radio interface No

IR interface No

Updateable Yes

Visualization Yes

Web-Server Yes

Use

System technology	2-wire
-------------------	--------

Safety

Degree of contamination	2
-------------------------	---

Protection index IP	IP20
---------------------	------

Protection class	isol.class II
------------------	---------------

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Storage/transport temperature	-25...70 °C (storage at > 45°C reduces the service life)
-------------------------------	--

Relative humidity (without condensation)	85 % at 25 °C
--	---------------