



TR131A



Media coupler, white, KNX

Technical properties

Architecture

Fixing mode surface-mounting

Connectivity

Radio protocol KNX Radio

Receiver category 2

Voltage

Operating voltage over bus 30 V DC

Dimensions

Dimensions (LLxwwxhh) 203 x 77 x 26,5 mm

Frequency

Transmission frequency 868 MHz

Radio transmission frequency 868.3 MHz

Power

Total power loss under IN 2 W

Radio transmission power < 25 mW

Materials

Colour white

RAL colour RAL 9010 - Pure white

Connection

Type of connection to the bus TG008 connector

Number of radio channel outputs max. 512

Bus connection bus connection via connecting terminal

Equipment

Number of radio channel inputs max. 512

Use conditions

Operating temperature 0...45 °C

Instructions

Information text

As line coupler for expansion of a KNX system with a KNX radio lead. ; As programming interface: in purely KNX radio systems, the surface-mounted KNX radio/TP gateway can be removed after parameterisation.