



TCC521E

IP41

## Presence detector 360° monobloc KNX / DALI

### Technical properties

#### Architecture

Bus system	KNX
------------	-----

#### Connectivity

Number of binary inputs	0
-------------------------	---

#### Voltage

Operating voltage over bus	21...32 V DC
----------------------------	--------------

#### Electric current

Bus current consumption (data transfer)	12 mA
---	-------

#### Dimensions

Dimensions (Ø x H)	78 x 70 mm
Installation opening Ø	60...63 mm
Recommended installation height	2.5...3.5 m
Installation wall thickness	10...28 mm

#### Measurement

Detection Method	presence
------------------	----------

#### Detection

Detection angle	360 °
Angle of vertical detection	55 °
Detection field Ø, on floor	≈ 7 m
Detection field Ø, at desk height	≈ 5 m
Frontal detecting distance	7 m
Side detecting distance	8 m

#### Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	PC-ABS
Surface appearance	matt

#### Lighting control

Brightness measurement range	5 / 1000 Lux
------------------------------	--------------

#### Installation, mounting

Maximum Mounting Height	4 m
-------------------------	-----

**Connection**

Conductor cross-section (flexible)	0.5...15 mm <sup>2</sup>
Conductor cross-section (rigid)	0.5...15 mm <sup>2</sup>
Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal

**Settings**

Supported configuration modes	system
Delay time, adjustable	1 mn...1 h

**Scope of delivery**

Bus connection included	Yes
-------------------------	-----

**Equipment**

Number of channels	1
Angle of horizontal detection	360 °

**Use conditions**

Operating temperature	-10...45 °C
Storage/transport temperature	-20...60 °C

**Identification**

Main design line	KNX
------------------	-----