



TCC530E

IP41 

Presence detector 360° monobloc KNX multi-channels

Technical properties

Architecture

Bus system	KNX
------------	-----

Controls and indicators

Button / push-button	with programming button
----------------------	-------------------------

Connectivity

Number of binary inputs	0
-------------------------	---

Voltage

Operating voltage over bus	21...32 V DC
----------------------------	--------------

Dimensions

Dimensions (Ø x H)	78 x 70 mm
Installation opening Ø	60...63 mm
Recommended installation height	2.5...3.5 m
Installation wall thickness	10...28 mm

Measurement

Detection Method	presence
------------------	----------

Detection

Detection angle	360 °
Detection angle	360 °
Angle of vertical detection	55 °
Detection field Ø, on floor	≈ 7 m
Detection field Ø, at desk height	≈ 5 m
Frontal detecting distance	7 m
Side detecting distance	8 m

Materials

Colour	white
RAL colour	RAL 9010 - Pure white
Material	PC-ABS
Surface appearance	matt

Lighting control

Brightness measurement range	5 / 1000 Lux
------------------------------	--------------

Installation, mounting

Maximum Mounting Height	4 m
-------------------------	-----

Connection	
Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal
Settings	
Supported configuration modes	system
Delay time, adjustable	1 mn...1 h
Scope of delivery	
Bus connection included	Yes
Equipment	
Number of channels	2
Angle of horizontal detection	360 °
Use conditions	
Operating temperature	-10...45 °C
Storage/transport temperature	-20...60 °C
Identification	
Main design line	KNX