



TXA112



Power supply 30V DC 640 mA

Technical properties

Architecture

Fixing mode Din-Rail

Configuration

Number of modules 4

Connectivity

Bus lines 1

Main electrical features

Frequency 50/60 Hz

Voltage

Output voltage 28...32 V

Filtered output voltage 30V +/- 2V

Electric current

Output current max. 640 mA

Output intensity 640 mA

Dimensions

Depth of installed product 64 mm

Height of installed product 90 mm

Length 64 mm

Width of installed product 72 mm

Power

Total power loss under IN 15 W

Materials

Colour stone grey

RAL colour RAL 7035 - Light grey

Connection

Conductor cross-section (flexible) 0.75...2.5 mm²

Conductor cross-section (rigid) 0.75...2.5 mm²

Equipment

Number of outputs 1

Use

Differentiation characteristic 1 - Sales with labelling field

Safety

Protection index IP

IP20

Use conditions

Operating temperature

-5...45 °C

Storage/transport temperature

-20...70 °C