



TXA112

IP20

**Power supply 30V DC 640 mA**

### Technical properties

#### Architecture

Bus system	EIB
------------	-----

#### Configuration

Number of modules	4
-------------------	---

#### Connectivity

Bus lines	1
-----------	---

#### Main electrical features

Frequency	50/60 Hz
-----------	----------

#### Voltage

Output voltage	30 V
----------------	------

Output voltage	28...32 V
----------------	-----------

Filtered output voltage	30V +/- 2V
-------------------------	------------

#### Electric current

Output current	max. 640 mA
----------------	-------------

Output intensity	640 mA
------------------	--------

#### Dimensions

Depth of installed product	64 mm
----------------------------	-------

Height of installed product	90 mm
-----------------------------	-------

Length	64 mm
--------	-------

Width of installed product	72 mm
----------------------------	-------

#### Power

Total power loss under IN	15 W
---------------------------	------

#### Materials

RAL colour	RAL 7035 - Light grey
------------	-----------------------

#### Connection

Connection cross-sect. flexible conductor	0,75 / 2,5mm <sup>2</sup>
---	---------------------------

Connection cross-sect. rigid cable	0,75 / 2.5mm <sup>2</sup>
------------------------------------	---------------------------

Conductor cross-section (flexible)	0.75...2.5 mm <sup>2</sup>
------------------------------------	----------------------------

Conductor cross-section (rigid)	0.75...2.5 mm <sup>2</sup>
---------------------------------	----------------------------

Type of connection	quick connect
--------------------	---------------

#### Equipment

**Use**

Differentiation characteristic 1 - Sales

with labelling field

**Use conditions**

Operating temperature

-5...45 °C

Storage/transport temperature

-20...70 °C