



TXA116



Power supply 2x 30V DC KNX 640 mA

Technical properties

Architecture

Fixing mode	Din-Rail
-------------	----------

Configuration

Number of modules	4
-------------------	---

Connectivity

Bus lines	2
-----------	---

Main electrical features

Frequency	50/60 Hz
-----------	----------

Voltage

Output voltage	28...32 V
----------------	-----------

Electric current

Output current	max. 640 mA
Output intensity	320 mA

Dimensions

Depth of installed product	64 mm
Height of installed product	90 mm
Length	64 mm
Width of installed product	72 mm
Width of rail mounted device (RMD)	4 modules

Power

Total power loss under IN	3.5 W
---------------------------	-------

Materials

RAL colour	RAL 7035 - Light grey
------------	-----------------------

Connection

Conductor cross-section (flexible)	0.75...2.5 mm ²
Conductor cross-section (rigid)	0.75...2.5 mm ²
Connection	protected earth conductor must be connected

Use

Differentiation characteristic 1 - Sales	with labelling field
--	----------------------

Safety

Protection index IP	IP20
---------------------	------

REACH conform	Yes
RoHS conform	Yes
Use conditions	
Operating temperature	-5...45 °C
Storage/transport temperature	-20...70 °C