




TX510

**IP41**



**Presence detector 360° KNX, 2 channels, with BCU**

**Technical properties**

**Architecture**

Bus system KNX

**Functions**

Function Switching functions, dimming functions, blind control functions, value transmitter functions, forced control functions, scene functions, heating functions and timer functions, 2 channel mode

**Configuration**

Channels Channel 1 für brightness-dependent or semiautomatic control (switching on via push-button) of consumers ; Channel 2 für brightness-independent control of consumers with predefined switch-on delay and delay time (3 operating modes)

**Connectivity**

Number of binary inputs 0

**Voltage**

Operating voltage over bus 21...32 V DC

**Electric current**

Bus current consumption (data transfer) 12 mA

Bus current consumption (idle) 12 mA

**Dimensions**

Dimensions (Ø x H) 110 x 44 mm

Recommended installation height 2.5...3.5 m

**Measurement**

Detection Method presence

**Detection**

Detection angle 360 °

Angle of vertical detection 55 °

Frontal detecting distance 7 m

Side detecting distance 6 m

**Materials**

Colour white

RAL colour RAL 9010 - Pure white

Surface appearance matt

**Lighting control**

Subject to technical modifications

**Installation, mounting**

Maximum Mounting Height	4 m
-------------------------	-----

Installation mode	for ceiling mounting in 60 surface-mounted or hollow-wall box
-------------------	---

**Connection**

Bus coupling unit	with integral bus coupling unit
-------------------	---------------------------------

Bus connection	bus connection via connecting terminal
----------------	--

**Settings**

Supported configuration modes	system, easy
-------------------------------	--------------

Delay ON	30 s
----------	------

HVAC-channel adjustable	≈ 30 s ... 60 mn
-------------------------	------------------

Delay time, adjustable	≈ 1...30 mn
------------------------	-------------

Setting	with potentiometers for setting the response brightness and delay time without dismantling
---------	--

**Scope of delivery**

Bus connection included	Yes
-------------------------	-----

**Accessories included**

Extension	Expansion of detection area possible by means of one or more detectors
-----------	--

**Equipment**

Number of channels	1
--------------------	---

Switch on delay HVAC-channel	15 mn
------------------------------	-------

Angle of horizontal detection	360 °
-------------------------------	-------

Slewing	Detector head slewing by 90°
---------	------------------------------

**Safety**

REACH conform	Yes
---------------	-----

RoHS conform	Yes
--------------	-----

**Use conditions**

Operating temperature	0...45 °C
-----------------------	-----------

Storage/transport temperature	-10...60 °C
-------------------------------	-------------

Energy-saving	energy saving by presence and brightness-controlled lighting control
---------------	--

**Identification**

Main design line	KNX
------------------	-----