



TXA204B

Output 4 -fold 10A

Technical properties

Architecture

Fixing mode	Din-Rail
-------------	----------

Functions

Multi-phase mode	suitable to switch different external conductors
------------------	--

Configuration

Number of modules	4
-------------------	---

Controls and indicators

Indicator lamp	yes
----------------	-----

Main electrical features

Rated operational voltage Ue	207 / 230 / 264 V
------------------------------	-------------------

Voltage

Operating voltage over bus	21...32 V DC
----------------------------	--------------

System supply voltage	30V DC via bus
-----------------------	----------------

Electric current

Number of entry circuits	0
--------------------------	---

Maximum through current	10 A
-------------------------	------

Rated current	10 A
---------------	------

Power

Max. power with electronic transfo.	1000 W
-------------------------------------	--------

Total power loss under IN	8 W
---------------------------	-----

Output power	1200 W
--------------	--------

Max. switching power	3600 W
----------------------	--------

Materials

Colour	stone grey
--------	------------

Fluorescent bulbs control

Max. power fluo. duo lamp comp. series	15 x 36 W
--	-----------

Incandescent bulbs control

Max. power with incandescent lamps	1200 W
------------------------------------	--------

Connection

Bus coupling unit	with integral bus coupling unit
-------------------	---------------------------------

Bus connection	bus connection via connecting terminal
----------------	--

Scope of delivery	
Bus connection included	Yes
Equipment	
Number of outputs	4
Bidirectional radio frequency	No
Modular expandability	No
Safety	
Protection index IP	IP20
Use conditions	
Operating temperature	0...45 °C
Storage/transport temperature	-20...70 °C
Identification	
Main design line	KNX