



TXA112



Power supply 30V DC 640 mA

Technical properties

Architecture

Fixing mode	Din-Rail
-------------	----------

Configuration

Number of modules	4
-------------------	---

Connectivity

Bus lines	1
-----------	---

Main electrical features

Frequency	50/60 Hz
-----------	----------

Voltage

Output voltage	28...32 V
Filtered output voltage	30V +/- 2V

Electric current

Output current	max. 640 mA
Output intensity	640 mA

Dimensions

Depth of installed product	64 mm
Height of installed product	90 mm
Length	64 mm
Width of installed product	72 mm

Power

Total power loss under IN	15 W
---------------------------	------

Materials

Colour	stone grey
RAL colour	RAL 7035 - Light grey

Connection

Conductor cross-section (flexible)	0.75...2.5 mm ²
Conductor cross-section (rigid)	0.75...2.5 mm ²

Equipment

Number of outputs	1
-------------------	---

Use

Differentiation characteristic 1 - Sales	with labelling field
--	----------------------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-5...45 °C
Storage/transport temperature	-20...70 °C