



TXA207A

Output 10 -fold 4A

Technical properties

Architecture

Bus system	EIB
Fixing mode	Din-Rail

Functions

Multi-phase mode	suitable to switch different external conductors
------------------	--

Configuration

Number of modules	6
-------------------	---

Controls and indicators

Indicator lamp	yes
----------------	-----

Main electrical features

Rated operational voltage Ue	230 V
Rated current	4 A

Voltage

Operating voltage over bus	21...32 V DC
Output voltage	230 V~
System supply voltage	30V DC via bus

Electric current

Number of entry circuits	0
Maximum through current	4 A
Rated current	4 A

Power

Max. power with electronic transfo.	800 W
Total power loss under IN	2.5 W
Output power	800 W
Max. switching power	8000 W

Materials

Colour	stone grey
--------	------------

Fluorescent bulbs control

Max. power fluo. duo lamp comp. series	12 x 36 W
--	-----------

Incandescent bulbs control

Max. power with incandescent lamps	800 W
------------------------------------	-------

Connection

Connection cross-sect. flexible conductor	0,75 / 2,5mm ²
Connection cross-sect. rigid cable	0,75 / 2.5mm ²
Type of contacts	10NO
Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal
Type of connection	quick connect

Scope of delivery

Bus connection included	Yes
-------------------------	-----

Equipment

Number of outputs	10
Bidirectional radio frequency	No
Modular expandability	No

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	0...45 °C
Storage/transport temperature	-20...70 °C

Identification

Main design line	KNX
------------------	-----