



TXA114



24 V=

IP20

Power supply 1x 30V DC KNX + 1x 24V DC

Technical properties

Architecture

Bus system	EIB
------------	-----

Configuration

Number of modules	4
-------------------	---

Connectivity

Bus lines	1
-----------	---

Outputs	one output 30 V DC, 320 mA incl. choke ; one output 24 V, 640 mA
---------	--

Main electrical features

Frequency	50/60 Hz
-----------	----------

Voltage

Output voltage	24V+30V
----------------	---------

Output voltage	28...32 V
----------------	-----------

Electric current

Output current	max. 320 mA
----------------	-------------

Output intensity	320 mA
------------------	--------

Fuse

Fuse	with electronic short-circuit and overload protection
------	---

Dimensions

Depth of installed product	64 mm
----------------------------	-------

Height of installed product	90 mm
-----------------------------	-------

Length	64 mm
--------	-------

Width of installed product	72 mm
----------------------------	-------

Width of rail mounted device (RMD)	4 modules
------------------------------------	-----------

Power

Total power loss under IN	4.4 W
---------------------------	-------

LED control

LED	with green LED for display of power supply per output ; with red LED for display of short-circuit and overload protection per output
-----	--

Connection

Connection cross-sect. flexible conductor	0,75 / 2,5mm ²
---	---------------------------

Connection cross-sect. rigid cable	0,75 / 2,5mm ²
------------------------------------	---------------------------

Conductor cross-section (flexible)	0.75...2.5 mm ²
Conductor cross-section (rigid)	0.75...2.5 mm ²
Type of connection	with QuickConnect plug-in terminals
Connection	protected earth conductor must be connected
Use	
Differentiation characteristic 1 - Sales	with labelling field
Safety	
Protection index IP	IP20
Use conditions	
Operating temperature	-5...45 °C
Storage/transport temperature	-20...70 °C