



TXA116

IP20

Power supply 2x 30V DC KNX 640 mA

Technical properties

Architecture

Bus system EIB

Configuration

Number of modules 4

Connectivity

Bus lines 2

Outputs with 2 outputs incl. choke per output

Main electrical features

Frequency 50/60 Hz

Voltage

Output voltage 2x 30V

Output voltage 28...32 V

Electric current

Output current max. 640 mA

Output intensity 320 mA

Fuse

Fuse with electronic short-circuit and overload protection

Dimensions

Depth of installed product 64 mm

Height of installed product 90 mm

Length 64 mm

Width of installed product 72 mm

Width of rail mounted device (RMD) 4 modules

Power

Total power loss under IN 3.5 W

Materials

RAL colour RAL 7035 - Light grey

LED control

LED with green LED for display of power supply per output ; with red LED for display of short-circuit and overload protection per output

Connection

| | |
|---|---|
| Connection cross-sect. flexible conductor | 0,75 / 2,5mm ² |
| Connection cross-sect. rigid cable | 0,75 / 2.5mm ² |
| Conductor cross-section (flexible) | 0.75...2.5 mm ² |
| Conductor cross-section (rigid) | 0.75...2.5 mm ² |
| Type of connection | with QuickConnect plug-in terminals |
| Connection | protected earth conductor must be connected |

Use

| | |
|--|----------------------|
| Differentiation characteristic 1 - Sales | with labelling field |
|--|----------------------|

Safety

| | |
|---------------|-----|
| REACH conform | Yes |
| RoHS conform | Yes |

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | -5...45 °C |
| Storage/transport temperature | -20...70 °C |