



TXA210AN

Dimmer 1 channel 300W

Technical properties

Architecture

| | |
|-------------|----------|
| Bus system | KNX |
| Fixing mode | Din-Rail |

Configuration

| | |
|-------------------|---|
| Number of modules | 4 |
|-------------------|---|

Controls and indicators

| | |
|----------------|-----|
| Indicator lamp | yes |
|----------------|-----|

Main electrical features

| | |
|---------------|----------|
| Frequency | 50/60 Hz |
| Rated current | 1.3 A |

Voltage

| | |
|-----------------------|----------------|
| System supply voltage | 30V DC via bus |
|-----------------------|----------------|

Power

| | |
|---------------------------|------------|
| Incandescent bulb power | 20 / 300 W |
| Total power loss under IN | 2.3 W |
| Power of the variator | 0 / 300 W |

Materials

| | |
|--------|------------|
| Colour | stone grey |
|--------|------------|

Fluorescent bulbs control

| | |
|---------------------------|-----|
| Power lighting fluo lamps | 60W |
|---------------------------|-----|

LED control

| | |
|-----------|------|
| Power LED | 60 W |
|-----------|------|

Connection

| | |
|--------------------|---------------|
| Type of load | universal |
| Type of connection | quick connect |

Equipment

| | |
|-------------------------------|-----------|
| Type of dimmer | universal |
| Bidirectional radio frequency | No |

Safety

| | |
|---------------------|------|
| Protection index IP | IP20 |
|---------------------|------|

Use conditions

| | |
|-------------------------------|-------------|
| Operating temperature | 0...45 °C |
| Storage/transport temperature | -20...70 °C |