



TXA661A



## DIMMER 1 CHANNEL 300W NE

### Technical properties

#### Architecture

Bus system KNX

#### Functions

Multi-phase mode suitable to switch different external conductors

Function Learning function for optimised operation of compact fluorescent lamps and LED luminaires can be activated via the bus

Soft startup bulb-preserving soft startup

#### Configuration

Number of modules 4

#### Controls and indicators

Indicator lamp yes

Operation manual operation also possible without bus, e.g. on building site ; Manual operation can be activated via selection switch, thereby deactivation of the KNX function ; Manual operation per channel via button with integrated status LED, thereby lockout of KNX function

Indication / display status LED integrated in the manual operation button

Manual selection switches / push-buttons selection switch for manual/bus operation as well as load setting

Button / push-button with illuminated programming button

#### Main electrical features

Frequency 50/60 Hz

Rated current 4 mA

#### Voltage

Auxiliary voltage 230 V AC

Input voltage 230 V AC

Operating voltage over bus 21...32 V DC

System supply voltage 30V DC via bus

#### Electric current

Bus current consumption (data transfer) < 2.3 mA

#### Fuse

Fuse short-circuit and overload proof (electronic fuse) ; short-circuit proof and overload proof (display using LEDs) ; overheating protection (display using LEDs)

#### Dimensions

Subject to technical modifications

Width of rail mounted device (RMD) 4 modules

### Power

Dimmable conventional transformers	300 VA
Incandescent bulb power	300 W
Total power loss under IN	320 mW
Power dissipation per coil	180 mW
Power of the variator	300 W
Electronic transformers	300 W

### Fluorescent bulbs control

Quantity energy-saving lamps	per channel max. 8
Dimmable energy-saving lamps	60 W
Power lighting fluo lamps	60W

### LED control

Quantity of dimmable, 230 V retrofit LED lamps	per channel max. 8
Max number of LED/CFL lamps	8
Dimmable LED lamps	60 W
Power LED	60 W

LED Status LED integrated in manual operation button ;  
Overheating protection, display using LEDs ; Over-  
load protection, display via LED

### Incandescent bulbs control

230 V incandescent lamps and halogen lamps	300 W
--	-------

### Connection

Connection cross-sect. flexible conductor	0,5 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	0,75 / 2.5mm <sup>2</sup>
Type of load	universal
Conductor cross-section (flexible)	0.75...2.5 mm <sup>2</sup>
Conductor cross-section (rigid)	0.75...2.5 mm <sup>2</sup>
Bus coupling unit	with integral bus coupling unit
Type of connection	with QuickConnect plug-in terminals
Bus connection	bus connection via connecting terminal
Type of connection	quick connect

### Settings

Supported configuration modes	easy, system
Parameterisation	preset behaviour in the event of bus voltage failure/return

### Scope of delivery

Bus connection included	Yes
-------------------------	-----

### Equipment

Number of outputs	1
Type of dimmer	dimming actuator

Substation input	No
Power boost suitable	No
Modular expandability	No
Dimming principle	phase cut-on or cut-off according to load type, self-learning ; minimum/maximum dimming values per channel settable on device
low noise	very low noise
<b>Use</b>	
Local operation/hand operation	Yes
<b>Safety</b>	
REACH conform	No
RoHS conform	Yes
Halogen free	No
Protection	with overheating, overload and short-circuit protection
<b>Use conditions</b>	
Operating temperature	-5...45 °C
Storage/transport temperature	-20...70 °C
<b>Identification</b>	
Main design line	KNX