



TXA206A

## Output 6 -fold 4A

### Technical properties

#### Architecture

Fixing mode Din-Rail

#### Functions

Multi-phase mode suitable to switch different external conductors

#### Configuration

Number of modules 4

#### Controls and indicators

Indicator lamp yes

#### Main electrical features

Rated operational voltage  $U_e$  230 V

Rated current 4 A

#### Voltage

Operating voltage over bus 21...32 V DC

System supply voltage 30V DC via bus

#### Electric current

Number of entry circuits 0

Maximum through current 4 A

Rated current 4 A

#### Power

Max. power with electronic transfo. 800 W

Total power loss under IN 1 W

Output power 800 W

Max. switching power 4800 W

#### Materials

Colour stone grey

#### Fluorescent bulbs control

Max. power fluo. duo lamp comp. series 12 x 36 W

#### Incandescent bulbs control

Max. power with incandescent lamps 800 W

#### Connection

Bus coupling unit with integral bus coupling unit

Bus connection

bus connection via connecting terminal

---

**Scope of delivery**

Bus connection included Yes

---

**Equipment**

Number of outputs 6

Bidirectional radio frequency No

Modular expandability No

---

**Safety**

Protection index IP IP20

---

**Use conditions**

Operating temperature 0...45 °C

Storage/transport temperature -20...70 °C

---

**Identification**

Main design line KNX