



TXA207B

Output 10 -fold 10A

Technical properties

Architecture

Bus system EIB

Functions

Multi-phase mode suitable to switch different external conductors

Configuration

Number of modules 6

Controls and indicators

Indicator lamp yes

Main electrical features

Rated operational voltage U_e 230 V

Rated current 10 A

Voltage

Operating voltage over bus 21...32 V DC

Output voltage 230 V~

System supply voltage 30V DC via bus

Electric current

Number of entry circuits 0

Maximum through current 10 A

Rated current 10 A

Power

Max. power with electronic transfo. 1000 W

Total power loss under IN 7.5 W

Output power 1200 W

Max. switching power 9000 W

Fluorescent bulbs control

Max. power fluo. duo lamp comp. series 15 x 36 W

Incandescent bulbs control

Max. power with incandescent lamps 1200 W

Connection

Connection cross-sect. flexible conductor 0,75 / 2,5mm²

Connection cross-sect. rigid cable 0,75 / 2.5mm²

Type of contacts	10NO
Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal
Type of connection	quick connect
Scope of delivery	
Bus connection included	Yes
Equipment	
Number of outputs	10
Bidirectional radio frequency	No
Modular expandability	No
Use conditions	
Operating temperature	0...45 °C
Storage/transport temperature	-20...70 °C
Identification	
Main design line	KNX