



TXA207C

## Output 10 -fold 16A

### Technical properties

#### Architecture

Bus system	EIB
------------	-----

#### Functions

Multi-phase mode	suitable to switch different external conductors
------------------	--

#### Configuration

Number of modules	6
-------------------	---

#### Controls and indicators

Indicator lamp	yes
----------------	-----

#### Main electrical features

Rated operational voltage Ue	230 V
Rated current	16 A

#### Voltage

Operating voltage over bus	21...32 V DC
Output voltage	230 V~
System supply voltage	30V DC via bus

#### Electric current

Number of entry circuits	0
Maximum through current	16 A
Rated current	16 A

#### Power

Max. power with electronic transfo.	1200 W
Total power loss under IN	15 W
Output power	2300 W
Max. switching power	14375 W

#### Fluorescent bulbs control

Max. power fluo. duo lamp comp. series	20 x 36 W
--	-----------

#### Incandescent bulbs control

Max. power with incandescent lamps	2300 W
------------------------------------	--------

#### Connection

Connection cross-sect. flexible conductor	0,75 / 2,5mm <sup>2</sup>
Connection cross-sect. rigid cable	0,75 / 2.5mm <sup>2</sup>

Type of contacts	10NO
Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal
Type of connection	quick connect
<b>Scope of delivery</b>	
Bus connection included	Yes
<b>Equipment</b>	
Number of outputs	10
Bidirectional radio frequency	No
Modular expandability	No
<b>Use conditions</b>	
Operating temperature	0...45 °C
Storage/transport temperature	-20...70 °C
<b>Identification</b>	
Main design line	KNX