



TXB202A

## 2 flush mounted output 4A twisted pair

### Technical properties

#### Architecture

Bus system	KNX
Fixing mode	flush-mounting

#### Functions

Multi-phase mode	suitable to switch different external conductors
------------------	--

#### Configuration

Number of modules	0
-------------------	---

#### Controls and indicators

Indicator lamp	yes
----------------	-----

#### Main electrical features

Rated operational voltage Ue	215 / 250 / 285 V
------------------------------	-------------------

#### Voltage

Operating voltage over bus	21...32 V DC
System supply voltage	30V DC via bus

#### Electric current

Number of entry circuits	0
Maximum through current	4 A
Rated current	4 A

#### Power

Max. power with electronic transfo.	600 W
Output power	600 W
Max. switching power	1200 W

#### Incandescent bulbs control

Max. power with incandescent lamps	600 W
------------------------------------	-------

#### Connection

Type of contacts	1NO
Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal

#### Scope of delivery

Bus connection included	Yes
-------------------------	-----

#### Equipment

Subject to technical modifications

Number of outputs	2
Bidirectional radio frequency	No
Modular expandability	No
<b>Safety</b>	
Protection index IP	IP20
<b>Use conditions</b>	
Operating temperature	0...45 °C
Storage/transport temperature	-20...70 °C
<b>Identification</b>	
Main design line	KNX