


TXA304



Binary input 4 fold, 230V~, modular, KNX

Technical properties

Architecture

Fixing mode Din-Rail

Functions

Bus module detachable No

Easy link functions Switching functions, dimming functions, blind control functions functions, priority functions, scene functions, heating functions and timer functions

ETS additional functions ETS additional functions: value transmitter 1 and 2 bytes, 2-channel mode, level switch function

Configuration

Number of modules 4

Controls and indicators

Command by lighting push buttons 10 mA

Voltage

Input voltage 230 V

Input voltage 230 V AC

Operating voltage over bus 21...32 V DC

Signal voltage 230 V AC

Type of input voltage AC

Electric current

Number of entry circuits 4

Dimensions

Depth of installed product 69 mm

Height of installed product 90 mm

Length 35 mm

Width of installed product 71 mm

Width of rail mounted device (RMD) 4 modules

Length

Max distance to switches 100 mm

Power

Total power loss under IN 0.1 W

Materials

Colour stone grey

Material plastic

Installation, mounting

Mounting type din-Rail

Connection

Conductor cross-section (flexible) 0.75...2.5 mm²

Conductor cross-section (rigid) 0.75...2.5 mm²

Connection to push-button / switch

Bus coupling unit with integral bus coupling unit

Bus connection bus connection via connecting terminal

Settings

Supported configuration modes system

Equipment

Number of outputs 0

Safety

Protection index IP IP20

Use conditions

Operating temperature 0...45 °C

Storage/transport temperature -20...70 °C

Identification

Main design line KNX