



TXA661B



DIMMER 1 CHANNEL 600W NE

Technical properties

Architecture

Fixing mode REG

Functions

Multi-phase mode suitable to switch different external conductors

Soft startup bulb-preserving soft startup

Configuration

Number of modules 4

Controls and indicators

Indicator lamp yes

Operation manual operation also possible without bus, e.g. on building site

Manual selection switches / push-buttons selection switch for manual/bus operation as well as load setting

Main electrical features

Frequency 50/60 Hz

Rated current 4 mA

Voltage

Auxiliary voltage 230 V AC

Input voltage 230 V AC

Operating voltage over bus 21...32 V DC

System supply voltage 30V DC via bus

Electric current

Bus current consumption (data transfer) < 2.3 mA

Fuse

Fuse short-circuit and overload proof (electronic fuse),
overheating protection (display using LEDs)

Dimensions

Width of rail mounted device (RMD) 4 modules

Power

Dimmable conventional transformers 600 VA

Incandescent bulb power 600 W

Total power loss under IN 320 mW

Power dissipation per coil 180 mW

Power of the variator	600 W
Electronic transformers	600 W
Materials	
Colour	light grey
Fluorescent bulbs control	
Quantity energy-saving lamps	per channel max. 8
Dimmable energy-saving lamps	120 W
Power lighting fluo lamps	120W
LED control	
Quantity of dimmable, 230 V retrofit LED lamps	per channel max. 8
Max number of LED/CFL lamps	10
Dimmable LED lamps	120 W
Power LED	120 W
Incandescent bulbs control	
230 V incandescent lamps and halogen lamps	600 W
Connection	
Type of load	universal
Conductor cross-section (flexible)	0.75...2.5 mm ²
Conductor cross-section (rigid)	0.75...2.5 mm ²
Bus coupling unit	with integral bus coupling unit
Bus connection	bus connection via connecting terminal
Settings	
Supported configuration modes	system
Scope of delivery	
Bus connection included	Yes
Equipment	
Number of outputs	1
Type of dimmer	dimming actuator
Substation input	No
Power boost suitable	No
Modular expandability	No
Dimming principle	phase cut-on or cut-off according to load type, self-learning
low noise	very low noise
Use	
Local operation/hand operation	Yes
Safety	
Protection index IP	IP20
Use conditions	

Subject to technical modifications

Operating temperature

-5...45 °C

Storage/transport temperature

-20...70 °C

Identification

Main design line

KNX