



TYB601A



1 flush mounted output 4A twisted pair

Technical properties

Architecture

Bus system	KNX
Fixing mode	flush-mounting

Configuration

Number of modules	0
-------------------	---

Controls and indicators

Indicator lamp	yes
----------------	-----

Main electrical features

Rated operational voltage Ue	230 V
Frequency	50/60 Hz
Rated current	4 A

Voltage

Max. switching capacity at	230 V AC
Operating voltage over bus	21...32 V DC
System supply voltage	30V DC via bus

Electric current

Bus current consumption (data transfer)	≈ 7 mA
Bus current consumption (idle)	5 mA
Number of entry circuits	0
Maximum through current	4 A
Rated current	4 A
Switching current at $\cos \varphi = 0.8$	max. 4 A

Dimensions

Height of installed product	29 mm
Dimensions (Ø x H)	53 x 29 mm
Width of rail mounted device (RMD)	0 modules
Height	29 mm

Power

Max. power with electronic transfo.	600 W
Output power	600 W
Max. switching power	600 W
Conventional transformers	600 VA
Electronic transformers	600 W

Materials

Colour	light grey
--------	------------

Lighting control

Fluorescent lamps with electronical ballast (EB)	6 x 58 W
--	----------

Fluorescent bulbs control

Energy-saving lamps	6 x 18 W
---------------------	----------

Power lighting fluo lamps	6 x 18W
---------------------------	---------

Max. power fluo. duo lamp comp. series	12 x 36 W
--	-----------

LED control

Power LED	108 W
-----------	-------

Incandescent bulbs control

Max. power with incandescent lamps	600 W
------------------------------------	-------

230 V incandescent lamps	600 W
--------------------------	-------

230 V halogen lamps	600 W
---------------------	-------

230 V incandescent lamps and halogen lamps	600 W
--	-------

Connection

Conductor cross-section (flexible)	0.75...2.5 mm ²
------------------------------------	----------------------------

Conductor cross-section (rigid)	0.75...2.5 mm ²
---------------------------------	----------------------------

Type of contacts	1NO
------------------	-----

Bus coupling unit	with integral bus coupling unit
-------------------	---------------------------------

Type of connection	with screw terminals
--------------------	----------------------

Bus connection	bus connection via connecting terminal
----------------	--

Settings

Supported configuration modes	system
-------------------------------	--------

Scope of delivery

Bus connection included	Yes
-------------------------	-----

Accessories included

Box	installation in flush-mounted or splash-protected junction box
-----	--

Equipment

Modular expandability	No
-----------------------	----

Use

Differentiation characteristic 3 - Sales	with screw-in lift terminals
--	------------------------------

Safety

Protection index IP	IP20
---------------------	------

Use conditions

Operating temperature	-5...45 °C
-----------------------	------------

Storage/transport temperature	-20...70 °C
-------------------------------	-------------

