




TYB673B



**KNX LED Controller 3 Channels constant current**

**Technical properties**

**Architecture**

Bus system	KNX
Fixing mode	flush-mounting

**Functions**

Number of function channels	3
Bus module detachable	No

**Configuration**

Number of modules	0
-------------------	---

**Controls and indicators**

Indicator lamp	yes
Button / push-button	with programming button and red programming LED

**Main electrical features**

Rated current	12 mA
---------------	-------

**Voltage**

Input voltage	< 24 V DC
Operating voltage over bus	21...32 V DC

**Electric current**

Bus current consumption (data transfer)	max. 12 mA
Maximum through current	2 A

**Fuse**

Fuse	overheating protection (display using LEDs)
------	---

**Dimensions**

Width of rail mounted device (RMD)	0 modules
------------------------------------	-----------

**Incandescent bulbs control**

Max. power with incandescent lamps	155 W
------------------------------------	-------

**Connection**

Conductor cross-section (flexible)	0.75...1.5 mm <sup>2</sup>
Conductor cross-section (rigid)	0.75...1.5 mm <sup>2</sup>
Bus coupling unit	with integral bus coupling unit
Type of connection	with screw terminals
Bus connection	bus connection via connecting terminal

**Cable**

---

Load cable length	max. 10 m
-------------------	-----------

**Settings**

---

Supported configuration modes	system
-------------------------------	--------

**Scope of delivery**

---

Bus connection included	Yes
-------------------------	-----

**Equipment**

---

Number of outputs	1
-------------------	---

---

Number of inputs	1
------------------	---

---

Substation input	No
------------------	----

---

Modular expandability	No
-----------------------	----

---

Interface 1-10 V	No
------------------	----

**Use**

---

Differentiation characteristic 3 - Sales	with screw terminals
--	----------------------

**Safety**

---

Protection index IP	IP20
---------------------	------

**Use conditions**

---

Operating temperature	-5...45 °C
-----------------------	------------

---

Storage/transport temperature	-20...70 °C
-------------------------------	-------------

**Identification**

---

Main design line	KNX
------------------	-----

**Instructions**

---

Special note text	Set direct current supply before connecting supply voltage for the first time with help of DIP-switch ; Caution! Connected loads depend on external LED power supply. Observe manufacturer's data.
-------------------	--