



TYF656T



Module 6 outputs for hot water heating KNX

Technical properties

Architecture

Bus system KNX

Functions

Multi-phase mode for 1 phase operation

Configuration

Number of modules 4

Controls and indicators

Button / push-button with programming button and red programming LED

Connectivity

Number of binary inputs 0

Main electrical features

Frequency 50/60 Hz

Voltage

Auxiliary voltage 110...230 V AC

Operating voltage over bus 21...32 V DC

Switching voltage 24...230 V

Electric current

Max. switching current (cos phi = 0.6) 1.5 A

Power

Total power loss under IN 1 W

Power dissipation per coil 0.4 W

Connection

Bus coupling unit with integral bus coupling unit

Bus connection bus connection via connecting terminal

Settings

Supported configuration modes system

Scope of delivery

Bus connection included Yes

Equipment

Modular expandability No

Use

Differentiation characteristic 3 - Sales

with screw terminals

Safety

Protection index IP

IP20

Use conditions

Operating temperature

-5...45 °C

Storage/transport temperature

-20...70 °C