



TYF656T



Module 6 outputs for hot water heating KNX

Technical properties

Architecture

| | |
|-------------|----------|
| Bus system | KNX |
| Fixing mode | Din-Rail |

Configuration

| | |
|-------------------|---|
| Number of modules | 4 |
|-------------------|---|

Controls and indicators

| | |
|----------------------|---|
| Button / push-button | with programming button and red programming LED |
|----------------------|---|

Connectivity

| | |
|-------------------------|---|
| Number of binary inputs | 0 |
|-------------------------|---|

Main electrical features

| | |
|-----------|----------|
| Frequency | 50/60 Hz |
|-----------|----------|

Voltage

| | |
|----------------------------|----------------|
| Auxiliary voltage | 110...230 V AC |
| Operating voltage over bus | 21...32 V DC |
| Switching voltage | 24...230 V |

Electric current

| | |
|--|-------|
| Max. switching current (cos phi = 0.6) | 1.5 A |
|--|-------|

Power

| | |
|----------------------------|-------|
| Total power loss under IN | 1 W |
| Power dissipation per coil | 0.4 W |

Materials

| | |
|--------|------------|
| Colour | light grey |
|--------|------------|

Connection

| | |
|-------------------|--|
| Bus coupling unit | with integral bus coupling unit |
| Bus connection | bus connection via connecting terminal |

Settings

| | |
|-------------------------------|--------|
| Supported configuration modes | system |
|-------------------------------|--------|

Scope of delivery

| | |
|-------------------------|-----|
| Bus connection included | Yes |
|-------------------------|-----|

Equipment

| | |
|--|----------------------|
| Modular expandability | No |
| Use | |
| Differentiation characteristic 3 - Sales | with screw terminals |
| Safety | |
| Protection index IP | IP20 |
| Use conditions | |
| Operating temperature | -5...45 °C |
| Storage/transport temperature | -20...70 °C |
| Identification | |
| Main design line | KNX |