



ADM416C

RCBO 4P 6kA B-16A 30mA A Class

Technical properties

Electric current

Rated current	16 A
Rated residual operating current I_{dn}	30 mA
Rated short-circuit breaking capacity I_{cn} under 400 V AC according to IEC 60898-1	6 kA
Rated current -25°C	19.40 A
Rated current at -20°C	19.10 A
Rated current -15°C	18.90 A
Rated current -10°C	18.60 A
Rated current -5°C	18.30 A
Rated current at 0°C	18 A
Rated current 5°C	17.60 A
Rated current 10°C	17.30 A
Rated current 15°C	17 A
Rated current at 20°C	16.70 A
Rated current 25°C	16.30 A
Rated current 30°C	16 A
Rated current 35°C	15.60 A
Rated current at 40°C	15.20 A
Rated current at 45°C	14.90 A
Rated current at 50°C	14.40 A
Rated current 55°C	14 A
Rated current 60°C	13.60 A

Architecture

Curve	B
Neutral position	Left, Right
Type of pole	4P
Number of protected poles	4

Capacity

Number of modules	4
-------------------	---

Safety

Residual current type	A
Ingress Protection (IP) class	IP2X

Voltage

Type voltage supply	AC
---------------------	----

Rated operational voltage Ue	230 - 400 V
Rated insulation voltage Ui	500 V
Dielectric strength value of power frequency	2 kV
Rated impulse withstand voltage Uimp	4,000 V
Overvoltage category according to IEC 60947-1	3

Installation, mounting

Nominal tightening torque top terminal	2 - 2 Nm
Nominal tightening torque down terminal	2 - 2 Nm
Nominal tightening torque	2 - 2 Nm
360° mounting position possible	Yes
Type of top connection for modular devices	Screw terminal
Type of bottom connection for modular devices	biconnect

Main electrical attributes

Rated short-circuit breaking capacity Icn AC according to IEC 60898-1	6 kA
---	------

Frequency

Frequency	50 - 50 Hz
-----------	------------

Connection

Cross-section of input with screws, for flexible conductors	1 - 16 mm²
Cross-section of input with screws, for massive conductors	1 - 25 mm²

Use conditions

Class of energy limitation I²t	3
Operating temperature	-25 - 40 °C

Dimensions

Height	84 mm
Width	71 mm
Depth	70 mm

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Power

Total power loss under IN	10.90 W
---------------------------	---------