



TYM616D



## Output module 16x 16A /230V~, KNX

### Technical properties

#### Architecture

Fixing mode REG

#### Functions

Multi-phase mode suitable to switch different external conductors

#### Configuration

Number of modules 8

#### Controls and indicators

Indicator lamp yes

Manual selection switches / push-buttons manual operation buttons for on/off (up/down) and bus function on/off per channel/device

#### Main electrical features

Rated operational voltage  $U_e$  230 V

Rated current 16 A

#### Voltage

Operating voltage over bus 21...32 V DC

System supply voltage 30V DC via bus

#### Electric current

Bus current consumption (data transfer) 5 mA

Bus current consumption (idle) 3 mA

Number of entry circuits 0

Rated current 16 A

#### Dimensions

Depth 65 mm

Width of rail mounted device (RMD) 8 modules

Height 90 mm

#### Power

Max. power with electronic transfo. 1500 W

Total power loss under IN 1.3 W

Output power 2300 W

Max. switching power 25300 W

Conventional transformers 1500 VA

Electronic transformers 1500 W

**Materials**

Colour	light grey
--------	------------

**Lighting control**

Fluorescent lamps with electronical ballast (EB)	20 x 36 W
--	-----------

- uncompensated	1200 VA
-----------------	---------

**Fluorescent bulbs control**

Energy-saving lamps	25 x 18 W
---------------------	-----------

Power lighting fluo lamps	25x18W
---------------------------	--------

Max. power fluo. duo lamp comp. series	27 X 36W
--	----------

Fluorescent lamps parallel compensated	1000 W /130 µF
--	----------------

**LED control**

Max number of LED/CFL lamps	25
-----------------------------	----

Power LED	450 W
-----------	-------

**Incandescent bulbs control**

Max. power with incandescent lamps	2300 W
------------------------------------	--------

230 V incandescent lamps	2300 W
--------------------------	--------

230 V halogen lamps	2300 W
---------------------	--------

230 V incandescent lamps and halogen lamps	2300 W
--	--------

**Connection**

Conductor cross-section (flexible)	0.5...4 mm <sup>2</sup>
------------------------------------	-------------------------

Conductor cross-section (rigid)	0.5...6 mm <sup>2</sup>
---------------------------------	-------------------------

Bus coupling unit	with integral bus coupling unit
-------------------	---------------------------------

Bus connection	bus connection via connecting terminal
----------------	--

**Settings**

Supported configuration modes	system
-------------------------------	--------

**Scope of delivery**

Bus connection included	Yes
-------------------------	-----

**Equipment**

Modular expandability	No
-----------------------	----

**Use**

Differentiation characteristic 3 - Sales	with screw-in lift terminals
--	------------------------------

**Safety**

Protection index IP	IP20
---------------------	------

**Use conditions**

Operating temperature	-5...45 °C
-----------------------	------------

Storage/transport temperature	-20...70 °C
-------------------------------	-------------

**Identification**

Main design line	KNX
------------------	-----