



VF122TF

**Small distributor,golf,flush,1row,22M,IP40,MS-terminal,PE,transparent door**

## Technical properties

### Architecture

|             |                |
|-------------|----------------|
| Fixing mode | flush-mounting |
|-------------|----------------|

### Functions

|                     |     |
|---------------------|-----|
| With a pipe-in lead | Yes |
|---------------------|-----|

### Configuration

|                   |    |
|-------------------|----|
| Number of modules | 22 |
|-------------------|----|

### Main electrical features

|                 |       |
|-----------------|-------|
| Nominal voltage | 400 V |
|-----------------|-------|

### Electric current

|               |      |
|---------------|------|
| Rated current | 63 A |
|---------------|------|

### Dimensions

|                             |         |
|-----------------------------|---------|
| Insertion depth             | 72 mm   |
| Depth of wall niche         | 72 mm   |
| Depth of installed product  | 97.5 mm |
| Internal depth              | 97.5 mm |
| Height of installed product | 293 mm  |
| Installation height         | 257 mm  |
| Width of installed product  | 532 mm  |
| Width in division units     | 22      |
| Built-in height             | 257 mm  |
| Built-in width              | 498 mm  |

### Cover, door

|                                    |                |
|------------------------------------|----------------|
| Type of door closing               | Latch          |
| Identification od protection index | 40             |
| Interlockable                      | No             |
| Number of keylock of the door      | 0              |
| Cover type                         | Closed (plain) |
| Door locking                       | without        |
| Door leave                         | single         |
| Cover type                         | Door           |
| Transparent cover or door          | Yes            |

### Materials

|        |            |
|--------|------------|
| Colour | pure white |
|--------|------------|

|   |                           |
|---|---------------------------|
| Colour  | white                     |
| Type of surface treatment                     | untreated                 |
| <b>Installation, mounting</b>                 |                           |
| Suitable for outdoor use                      | No                        |
| <b>Settings</b>                               |                           |
| Enclosure type                                | Distributor empty cabinet |
| <b>Equipment</b>                              |                           |
| Number of rows                                | 1                         |
| Quantity of section in width                  | 1                         |
| Quantity of rails                             | 1                         |
| Can be accessorized                           | Yes                       |
| Number of openings for flange plates          | 0                         |
| Extension possible                            | Yes                       |
| Earthing terminal block                       | Yes                       |
| Neutral terminal block                        | No                        |
| Signal passing door                           | Yes                       |
| <b>Standards</b>                              |                           |
| GWT Glow wire test                            | 650 °C                    |
| European directive WEEE                       | not concerned             |
| <b>Safety</b>                                 |                           |
| IK protection code against mechanical impacts | IK07                      |
| Protection class                              | isol.class II             |
| REACH conform                                 | No                        |
| RoHS conform                                  | Yes                       |
| Halogen free                                  | Yes                       |
| <b>Use conditions</b>                         |                           |
| Operating temperature                         | -25...40 °C               |