



CEA263N

RCCB 2P 63A 100mA A Class

Technical properties

Architecture

Type of pole	1P+N
--------------	------

Electric current

Rated current	63 A
Rated residual operating current I_{dn}	100 mA
Breaking and opening capacity I_{dm}	1.50 kA
Rated conditional short-circuit current I_{nc} according to EN61008-1	6 kA
Rated current -25°C	63 A
Rated current at -20°C	63 A
Rated current -15°C	63 A
Rated current -10°C	63 A
Rated current -5°C	63 A
Rated current at 0°C	63 A
Rated current 5°C	63 A
Rated current 10°C	63 A
Rated current 15°C	63 A
Rated current at 20°C	63 A
Rated current 25°C	63 A
Rated current 30°C	63 A
Rated current 35°C	63 A
Rated current at 40°C	63 A
Rated current at 45°C	63 A
Rated current at 50°C	63 A
Rated current 55°C	63 A
Rated current 60°C	56 A
Rated current 65°C	49 A
Rated current 70°C	40 A

Main electrical attributes

Nominal tightening torque top terminal	2.80 - 2.80 Nm
Nominal tightening torque down terminal	2.80 - 2.80 Nm

Voltage

Rated operational voltage U_e	230 - 230 V
Type voltage supply	AC
Rated insulation voltage U_i	500 V
Rated impulse withstand voltage U_{imp}	4,000 V

Frequency

Frequency	50 - 50 Hz
-----------	------------

Capacity

Number of modules	2
-------------------	---

Compatibility

Suitable for DIN Rail	Yes
-----------------------	-----

Safety

Residual current type	A
-----------------------	---

Ingress Protection (IP) class	IP20
-------------------------------	------

Installation, mounting

Type of top connection for modular devices	Screw terminal
--	----------------

Type of bottom connection for modular devices	biconnect
---	-----------

Nominal tightening torque	2.80 - 2.80 Nm
---------------------------	----------------

Connection

Cross-section of input and output with screws, for massive conductors	1 - 25 mm ²
---	------------------------

Cross-section of input and output with screws, for flexible conductors	1 - 16 mm ²
--	------------------------

Power

Total power loss under IN	8.70 W
---------------------------	--------

Use conditions

Max. Altitude	2,000 m
---------------	---------

Endurance

Electric endurance in number of cycles	2,000
--	-------

Number of mechanical operations	4,000
---------------------------------	-------

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Top connection alignment for modular devices	Aligned terminal
--	------------------

Down connection alignment for modular devices	Aligned terminal
---	------------------

Dimensions

Height	83 mm
--------	-------

Width	35 mm
-------	-------

Depth	70 mm
-------	-------