



VF312PF



Small distributor,golf,flush,3row,36M,IP40,MS-terminal,PE,white door

Technical properties

Architecture

Fixing mode	flush-mounting
-------------	----------------

Functions

With a pipe-in lead	Yes
Protection main switch	No

Configuration

Number of modules	36
-------------------	----

Main electrical features

Nominal voltage	400 V
-----------------	-------

Electric current

Rated current	63 A
---------------	------

Dimensions

Insertion depth	72 mm
Depth of wall niche	72 mm
Depth of installed product	97.5 mm
Internal depth	97.5 mm
Height of installed product	543 mm
Installation height	507 mm
Width of installed product	352 mm
Width in division units	12
Built-in height	507 mm
Built-in width	318 mm

Cover, door

Type of door closing	Latch
Identification of protection index	40
Interlockable	No
Number of keylock of the door	0
Cover type	Closed (plain)
Door locking	without
Door leave	single
Cover type	Door
Transparent cover or door	No

Materials

Colour	pure white
Colour	white
Type of surface treatment	untreated
Installation, mounting	
Suitable for outdoor use	No
Settings	
Enclosure type	Distributor empty cabinet
Scope of delivery	
Number of RCCB in enclosure	0
Equipment	
Number of rows	3
Quantity of section in width	1
Quantity of rails	3
Can be accessorized	Yes
Number of openings for flange plates	0
Extension possible	Yes
Earthing terminal block	Yes
Neutral terminal block	No
Signal passing door	Yes
Standards	
GWT Glow wire test	650 °C
European directive WEEE	not concerned
Safety	
IK protection code against mechanical impacts	IK07
Protection class	isol.class II
REACH conform	No
RoHS conform	Yes
Halogen free	Yes
Impact strength	IK07
Use conditions	
Operating temperature	-25...40 °C