



EC100

Hours counter

Technical properties

Capacity

Number of modules	2
-------------------	---

Frequency

Frequency	50 - 50 Hz
-----------	------------

Use conditions

Operating temperature	-10 - 45 °C
Storage/transport temperature	-20 - 60 °C

Connectivity

Type of connection	Screw terminal
--------------------	----------------

Connection

Cross-section flexible conductor	1 - 6 mm ²
Cross-section rigid conductor	1.5 - 10 mm ²

Dimensions

Height	90 mm
Width	35 mm
Depth	60 mm

Power supply

Supply voltage	230 V +/- 15%
----------------	---------------

Safety

Ingress Protection (IP) class	IP20
-------------------------------	------

Installation, mounting

Mounting on	DIN rail
-------------	----------

Equipment

Number of channels	6
--------------------	---